

Product information

83 20 010

Pipe Wrench 45°

DIN 5234

- Swedish pattern
- 45° angled jaws
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General

Article No.	83 20 010
EAN	4003773014218
Pliers	red powder-coated
Weight	817 g
Dimensions	320 x 49 x 20 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Clamping width	42 mm
Capacities for pipes (diameter)	Ø 1 5/8 Inch
Capacities for pipes (diameter)	Ø 42 mm
Capacities for nuts	42 mm
Inner diameter, inches	Ø 1 Inch

technical change and errors excepted

