

## Product information

# 83 20 020

## Pipe Wrench 45°

DIN 5234

- Swedish pattern
- 45° angled jaws
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



### General

|                 |                       |
|-----------------|-----------------------|
| Article No.     | 83 20 020             |
| EAN             | 4003773014232         |
| Pliers          | red powder-coated     |
| Weight          | 2,596 g               |
| Dimensions      | 570 x 72 x 28 mm      |
| Standard        | DIN 5234              |
| REACH compliant | does not contain SVHC |
| RoHS compliant  | not applicable        |

### Technical details

|                                 |              |
|---------------------------------|--------------|
| Clamping width                  | 70 mm        |
| Capacities for pipes (diameter) | Ø 2 3/4 Inch |
| Capacities for pipes (diameter) | Ø 70 mm      |
| Capacities for nuts             | 70 mm        |
| Inner diameter, inches          | Ø 2 Inch     |

*technical change and errors excepted*

