




**Part Number :** [2195620017](#)

**Product Description :** EXTreme Guardian HD Right-Angle Plug Assembly with Guide Pins, 2 Power Circuits, 30 Signal Circuits

**Series Number :** 219562

**Status :** Active

**Product Category :** Board-to-Board Connectors



---

## Documents & Resources

### Drawings

[Drawing 2195620017\\_sd.pdf](#)

### 3D Models and Design Files

[3D Model PDF 2195620017.pdf](#)

[3D Model 2195620017\\_stp.zip](#)


### Specifications

[Product Specification 2141130000-PS-000.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |   |
|--------------------|---|
| GADSL/IMDS         | Compliant with Exemption 44   |
| China RoHS         |  |
| EU ELV             | Not Relevant  |
| Low-Halogen Status | Low-Halogen per   |
| REACH SVHC         | Not Contained per D(2023)3788-DC (14 Jun 2023)  |
| EU RoHS            | Compliant per EU 2015/863   |

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

---

## Part Details

### General

|                |   |
|----------------|---|
| Status         | Active  |
| Category       | Board-to-Board Connectors   |
| Series         | 219562  |
| Description    | EXTreme Guardian HD Right-Angle Plug Assembly with Guide Pins, 2 Power Circuits, 30 Signal Circuits |
| Application    | Board-to-Board, Power, Signal   |
| Component Type | PCB Header  |
| Product Family | EXTreme Guardian System   |
| Product Name   | EXTreme Guardian HD   |
| UPC            | 196823042485  |

### Agency

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

### Electrical

|                               |        |
|-------------------------------|--------|
| Current - Maximum per Contact | 130.0A |
| Voltage - Maximum             | 125V   |

### Physical

|                                |       |
|--------------------------------|-------|
| Breakaway                      | No    |
| Circuits (Loaded)              | 32    |
| Circuits (maximum)             | 32    |
| Color - Resin                  | Black |
| Durability (mating cycles max) | 200   |
| First Mate / Last Break        | No    |
| Flammability                   | 94V-0 |
| Glow-Wire Capable              | No    |

|                                |                                |
|--------------------------------|--------------------------------|
| Guide to Mating Part           | Yes                            |
| Keying to Mating Part          | None                           |
| Lock to Mating Part            | No                             |
| Mated Height                   | 12.74mm                        |
| Material - Metal               | High Conductivity Copper       |
| Material - Plating Mating      | Gold                           |
| Material - Plating Termination | Tin                            |
| Material - Resin               | Liquid Crystal Polymer         |
| Net Weight                     | 17.200/g                       |
| Number of Rows                 | 1, 5                           |
| Orientation                    | Right Angle                    |
| Packaging Type                 | Tray                           |
| PC Tail Length                 | 2.53mm, 3.30mm                 |
| PCB Locator                    | Yes                            |
| PCB Retention                  | Yes                            |
| PCB Thickness - Recommended    | 1.58mm                         |
| Pitch - Mating Interface       | 5.78mm, 2.00mm                 |
| Plating min - Mating           | 0.762µm                        |
| Plating min - Termination      | 2.540µm                        |
| Polarized to Mating Part       | Yes                            |
| Polarized to PCB               | Yes                            |
| (p)ower-(s)ignal Configuration | 2p - 30s                       |
| Temperature Range - Operating  | -40° to +125°C, -40° to +105°C |
| Termination Interface Style    | Through Hole - Compliant Pin   |

---

## Mates With / Use With

### Mates with Part(s)

| Description  | Part Number       |
|--|-------------------|
| EXTreme Guardian HD Vertical Receptacle Assembly with Guide Receivers, 2 Power Circuits, 30 Signal Circuits    | <u>2195630017</u> |
| EXTreme Guardian HD Right-Angle Receptacle Assembly with Guide Receivers, 2 Power Circuits, 30 Signal Circuits | <u>2195640017</u> |

---

---

This document was generated on Sep 06, 2023