

## Han 1A OM 5+PE +latch m/ - PVC 5m



Image is for illustration purposes only. Please refer to product description.

Part number	33 40 080 0201 050
Specification	Han 1A OM 5+PE +latch m/ - PVC 5m
HARTING eCatalogue	<a href="https://b2b.harting.com/33400800201050">https://b2b.harting.com/33400800201050</a>

### Identification

Category	System cabling
Series	Han <sup>®</sup> 1A
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Han <sup>®</sup> 1A Male Overmoulded
Type of cable	Copper cable (round)
Description of the cable	Oil resistant

### Version

Cable length	5 m
Number of cores	6
Core structure	6x 1.5 mm <sup>2</sup>
Number of contacts	5
PE contact	Yes
Locking type	Snap-in latches
Details	IP66 / IP67 in mated cable to cable position

### Technical characteristics

Rated current	10 A
Rated voltage	400 V
Rated voltage conductor-earth	300 V



**Pushing Performance**  
Since 1945

## Technical characteristics

Limiting temperature	-30 ... +80 °C unmoved -15 ... +80 °C moved
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 mated condition IP66 mated condition IP67 mated condition
Cable diameter	9.2 mm

## Material properties

Material (cable)	PVC
Colour (cable)	Grey

## Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
----------------	--------------------------------

## Commercial data

Packaging size	2
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140237353
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line