

Han 1A OM 3+PE +latch m/ - PVC 3m



Image is for illustration purposes only. Please refer to product description.

Part number	33 40 040 0202 030
Specification	Han 1A OM 3+PE +latch m/ - PVC 3m
HARTING eCatalogue	https://b2b.harting.com/33400400202030

Identification

Category	System cabling
Series	Han [®] 1A
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Han [®] 1A Male Overmoulded
Type of cable	Copper cable (round)
Description of the cable	Oil resistant

Version

Cable length	3 m
Number of cores	4
Core structure	4x 2.5 mm ²
Number of contacts	3
PE contact	Yes
Details	IP66 / IP67 in mated cable to cable position

Technical characteristics

Rated current	16 A
Rated voltage	400 V
Rated voltage conductor-earth	300 V
Limiting temperature	-40 ... +80 °C unmoved -15 ... +80 °C moved



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 mated condition IP66 mated condition IP67 mated condition
Cable diameter	9.2 mm

Material properties

Material (cable)	PVC
Colour (cable)	Grey

Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
----------------	--------------------------------

Commercial data

Packaging size	2
Net weight	500 g
Country of origin	Romania
European customs tariff number	85444290
GTIN	5713140237063
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line