

## Han 1A OM 12 Pole +latch f/ - PVC 3m



Image is for illustration purposes only. Please refer to product description.

Part number	33 40 110 0703 030
Specification	Han 1A OM 12 Pole +latch f/ - PVC 3m
HARTING eCatalogue	<a href="https://b2b.harting.com/33401100703030">https://b2b.harting.com/33401100703030</a>

### Identification

Category	System cabling
Series	Han <sup>®</sup> 1A
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Han <sup>®</sup> 1A Female Overmoulded
Type of cable	Copper cable (round)
Description of the cable	Oil resistant

### Version

Cable length	3 m
Number of cores	12
Core structure	12x 0.5 mm <sup>2</sup>
Number of contacts	12
Locking type	Snap-in latches
Details	IP66 / IP67 in mated cable to cable position

### Technical characteristics

Rated current	6.5 A
Rated voltage	50 V
Limiting temperature	-40 ... +80 °C unmoved -5 ... +80 °C moved
Mating cycles	≥100



**Pushing Performance**  
Since 1945

## Technical characteristics

Degree of protection acc. to IEC 60529	IP65 mated condition
	IP66 mated condition
	IP67 mated condition
Cable diameter	8.7 mm

## Material properties

Material (cable)	PVC
Colour (cable)	Grey

## Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
----------------	--------------------------------

## Commercial data

Packaging size	1
Country of origin	Romania
European customs tariff number	85444290
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line