

Han 1A OM 12 Pole -lever m/ - PVC 5m



Image is for illustration purposes only. Please refer to product description.

Part number	33 40 100 0703 050
Specification	Han 1A OM 12 Pole -lever m/ - PVC 5m
HARTING eCatalogue	https://b2b.harting.com/33401000703050

Identification

Category	System cabling
Series	Han [®] 1A
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	Han [®] 1A Male Overmoulded
Type of cable	Copper cable (round)
Description of the cable	Oil resistant

Version

Cable length	5 m
Number of cores	12
Core structure	12x 0.5 mm ²
Number of contacts	12
Locking type	Single locking lever
Details	IP66 / IP67 in mated cable to cable position

Technical characteristics

Rated current	6.5 A
Rated voltage	50 V
Limiting temperature	-40 ... +80 °C unmoved -5 ... +80 °C moved
Mating cycles	≥100



Pushing Performance
Since 1945

Technical characteristics

Degree of protection acc. to IEC 60529	IP65 mated condition
	IP66 mated condition
	IP67 mated condition
Cable diameter	8.7 mm

Material properties

Material (cable)	PVC
Colour (cable)	Grey

Specifications and approvals

Specifications	IEC 60332-1-2 Flame retardancy
----------------	--------------------------------

Commercial data

Packaging size	1
Net weight	600 g
Country of origin	Romania
European customs tariff number	85444290
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line