

#### Part Number : 1731110365

Product Description : FCT Metal Backshell for D-Sub Connector, Shell Size 2, Straight Cable Outlet, with Rubber Bushing, 4-40 UNC Knurled Thumb Screws, and 4-40 UNC Locking Screws Series Number : 173111

Status : Active Product Category : D-Sub Backshells Engineering Number : FMH2-4381



### **Documents & Resources**

Drawings Drawing 1731110500\_sd.pdf

### **Product Environment Compliance**

#### Compliance

GADSL/IMDS	Not Relevant
China RoHS	<b>@</b>
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

### - chemSHERPA (xml)

## EU RoHS Certificate of Compliance

## Part Details

### General

Status	Active
Category	D-Sub Backshells
Series	173111
Description	FCT Metal Backshell for D-Sub Connector, Shell Size 2, Straight Cable Outlet, with Rubber Bushing, 4-40 UNC Knurled Thumb Screws, and 4-40 UNC Locking Screws
Product Family	FCT D-Sub Connectors
Product Name	FCT Products
Туре	Rugged Metal
UPC	191130024919

### Electrical

Shield Type	Solid Metal
Shielded	Yes

# Physical

Cable Diameter	5.00-8.50mm
Material - Backshell	Zinc Die-cast
Material - Bushing	TPE
Material - Screw	Brass
Mounting Style	Knurled Thumb Screw Lock
Net Weight	9.200/g
Orientation	Straight
Packaging Type	Tubular Foil
Plating - Backshell	Nickel
Temperature Range - Operating	-35° to +100°C
Thread Size	4-40 UNC
Thread Type	Standard
Tightening Test Torque	40 Ncm

Waterproof / Dustproof	No
------------------------	----

Use with Part(s)

Description	Part Number
Use With	FCT D-Sub, Size 2

This document was generated on Oct 04, 2023