

50cm (20in) USB to Lightning Cable, MFi Certified, Coiled iPhone Charger Cable, Black, Durable TPE Jacket Aramid Fiber, Heavy Duty Coil Lightning Cable

**Product ID:** RUSB2ALT50CMBC



This coiled Lightning to USB A cable can withstand the daily demands of charging and syncing your mobile devices. It contracts to 1ft (32cm) making it compact and convenient to store.

The durable Lightning charging cable has aramid fiber reinforcement that shelters it from the stress of frequent bends. This also lets the cable flex without over-stretching or damaging the core of the cable.

The Lightning to USB A cable is constructed to prevent the connector from separating from the jacket. The extra-long strain relief molding is tested to withstand over 5,000+ bend cycles at a 180 angle.

The durable cable supports all USB 2.0 specifications providing a dependable connection for all your Lightning devices. It is also Apple MFi certified which is guaranteed for fast and reliable charge and sync from USB-A charging ports.

RUSB2ALT50CMBC is backed by a StarTech.com 2-year warranty and free lifetime technical support.

## Certifications, Reports and Compatibility



## Applications

## Features

- **USB TO LIGHTNING CABLE:** Coiled cable stretches up to 20in (50cm) and contracts to 12.5in (32cm) preventing it from being tangled; Strong but soft flexible TPE jacket, makes it easy to coil and put away in vehicle console or glove compartment
- **RUGGED DESIGN:** High Quality USB A 2.0 cable reinforced with aramid fiber for increased tensile strength; Tested to withstand 10000+ insertions & 5000+ bend cycles at 180 Durable TPE jacket and strain relief; TPE is non-toxic, halogen free
- **APPLE MFI CERTIFIED:** USB-A to Lightning adapter cable for guaranteed fast & reliable charge/sync from USB-A charger port for Lightning devices including iPhone 13/12 Pro/Max/Mini, iPhone 8/11/11 Pro, iPhone XR, iPad Air, iPad, iPad Mini
- **CHARGE LIGHTNING DEVICES:** Coiled heavy duty cord charges devices with a Lightning port, includes AirPods, Magic Keyboard, Magic Trackpad, Magic Mouse & Siri Remote, ideal for use in Charging Stations
- **CABLE SPECS:** Length: 20in (50 cm) Color: Black Cable Type: Coiled Connectors: Lightning & USB A Performance: USB 2.0 480Mbps Reinforcement: Aramid Fiber Jacket Type: TPE Shield: Al-Mylar Heavy Duty iPhone Charging Cable

---

#### Hardware

Warranty	2 Years
Connector Plating	Nickel
Cable Jacket Material	TPE - Thermoplastic Elastomers
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

#### Performance

Maximum Cable Length	19.7 in [500 mm]
Type and Rate	USB 2.0 - 480 Mbit/s

---

#### Connector(s)

Connector A	1 - Apple Lightning Connector (8-pin)
Connector B	1 - USB 2.0 Type-A (4 pin, 480Mbps)

---

#### Environmental

Operating Temperature	0 to 80C (32 to 176F)
Storage Temperature	0 to 80C (32 to 176F)
Humidity	0% to 95% RH

---

#### Physical Characteristics

Color	Black
-------	-------

Wire Gauge	22/32 AWG
Cable Length	19.7 in [500 mm]
Cable OD	0.1 in [3.1 mm]
Product Length	13.2 in [33.6 cm]
Product Width	0.6 in [1.5 cm]
Product Height	0.3 in [7.0 mm]
Weight of Product	1.0 oz [28.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	5.0 in [12.7 cm]
Package Width	8.8 in [22.3 cm]
Package Height	0.7 in [1.7 cm]
Shipping (Package) Weight	1.1 oz [32.0 g]

---

**What's in the Box**

Included in Package	1 - USB-A to Lightning cable
---------------------	------------------------------

---

*\*Product appearance and specifications are subject to change without notice.*