

9 m (30 ft.) Active USB 2.0 A to B Cable

Product ID: USB2HAB30AC



This 30-foot USB A to B cable features one USB type-A connector and one USB type-B connector, providing a high-quality connection to USB 2.0 peripherals.

This USB cable is expertly designed with top quality materials, incorporating an equalizing chip, which enables it to perform beyond the limits of standard USB cables and communicate with peripherals up to 30 ft. away.

USB2HAB30AC is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connecting USB 2.0/1.1 devices up to 30ft away to a computer

Features

- Built-in equalizing chip enables USB 2.0 connections spanning 30ft

Hardware

Warranty

2 Years

Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

Performance

Maximum Cable Length	29.5 ft [9 m]
Type and Rate	USB 2.0 - 480 Mbit/s

Connector(s)

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB B (4 pin)

Special Notes / Requirements

Note	USB2HAB30AC draws a maximum of 70mA for powering internal active circuitry
------	--

Environmental

Operating Temperature	0-75C
Storage Temperature	5-35C
Humidity	60-90%

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	29.5 ft [9 m]
Product Length	29.5 ft [9.0 m]
Product Width	0.5 in [1.3 cm]
Product Height	0.2 in [5.6 mm]
Weight of Product	15.3 oz [433.0 g]

Packaging Information

Package Quantity	1
------------------	---

Package Length	5.5 in [14.0 cm]
Package Width	5.5 in [14.0 cm]
Package Height	2.7 in [6.8 cm]
Shipping (Package) Weight	1.1 lb [0.5 kg]

What's in the Box

Included in Package	1 - 9m/30ft High Speed Certified USB 2.0 Cable
---------------------	--

****Product appearance and specifications are subject to change without notice.***