

3m USB 2.0 A to B Cable - M/M

**Product ID:** USB2HAB3M



The USB2HAB3M 3-meter USB A-to-B cable features one USB 'A' male connector and one USB 'B' male connector, providing a high quality connection to USB 2.0 peripherals such as USB printers, scanners or external USB hard drives.

Constructed of only top quality materials and expertly designed for durability, this USB 2.0 A-B cable is backed by StarTech.com's Lifetime Warranty.

## Certifications, Reports and Compatibility



## Applications

- Use with any USB 2.0 rated device or add-on card
- Compatible with USB1.1 devices
- Replace worn-out or missing USB cables with this high quality cable

## Features

- High quality USB 'A' and USB 'B' connectors
- Supports USB 2.0 data transfer rates up to 480 Mbps

---

**Hardware**

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Connector(s)**

Connector A	1 - USB 2.0 Type-A (4 pin, 480Mbps)
Connector B	1 - USB B (4 pin)

---

**Physical Characteristics**

Color	Black
Wire Gauge	24/28 AWG
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	0.2 in [5.0 mm]
Product Height	0.2 in [5.0 mm]
Weight of Product	3.7 oz [104.2 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.7 in [22.2 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.4 in [1.0 cm]
Shipping (Package) Weight	3.7 oz [105.2 g]

---

**What's in the Box**

Included in Package	1 - 3 m USB 2.0 A to B Cable - M/M
---------------------	------------------------------------

---

*\*Product appearance and specifications are subject to change without notice.*