

USB 3.0 (5Gbps) Cable - A to A - M/M - 3 m (10 ft.)

**Product ID:** USB3SAA3MBK



This USB 3.2 Gen 1 (5Gbps) cable, also known as a USB 3.0 cable, lets you connect your USB-A devices as needed throughout your workspace. With a connection distance of up to 3 meters (10 feet), you can organize your PC and USB hub, or other USB-A devices, to match your configuration needs.

Plus, this high-quality cable features Shielded Twisted Pair (STP) construction, which helps to prevent electro-magnetic interference and ensure reliable data communication.

The USB3SAA3MBK is backed by StarTech.com's lifetime warranty for guaranteed reliability.

## Certifications, Reports and Compatibility



## Applications

- Connect your USB 3.0 USB-A devices, such as a USB hub, to a desktop or server

## Features

- Position your USB 3.2 Gen1 devices as needed throughout your workspace
- Molded connectors with strain relief
- Guaranteed reliability

---

**Hardware**

Warranty	Lifetime
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid

---

**Performance**

Type and Rate	USB 3.0 - 5 Gbit/s
---------------	--------------------

---

**Connector(s)**

Connector A	1 - USB Type-A (9 pin, 5 Gbps)
Connector B	1 - USB Type-A (9 pin, 5 Gbps)

---

**Physical Characteristics**

Color	Black
Connector Style	Straight
Wire Gauge	24/28 AWG
Cable Length	9.8 ft [3 m]
Product Length	9.8 ft [3.0 m]
Product Width	0.6 in [15.0 mm]
Product Height	0.3 in [0.8 cm]
Weight of Product	4.0 oz [112.0 g]

---

**Packaging Information**

Package Quantity	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.7 in [18.0 mm]
Shipping (Package) Weight	4.3 oz [122.0 g]

---

**What's in the Box**

Included in Package      1 - 3m USB 3.0 A to A Cable - M/M - Black

---

*\*Product appearance and specifications are subject to change without notice.*