

1 ft Coax HD15 VGA to 5 BNC RGBHV Monitor Cable - M/F

Product ID: VGABNCMF1



The VGABNCMF1 1-foot Coax HD15 VGA to 5 BNC RGBHV Adapter Cable features an HD15 VGA (male) connector and 5 BNC (RGBHV) (female) connectors, allowing you to connect your existing BNC video source to a VGA distribution amplifier or PC.

The cable can also be used with a VGA out signal, breaking out to 5 BNC female connectors that can be used with a 5 BNC (M-M) cable for use with a BNC monitor/display.

Certifications, Reports and Compatibility



Applications

- Connect your BNC connected cabled panels and projectors to a VGA distribution amplifier or PC

Features

- Short flexible cable design
- HD15 VGA Male to 5 BNC Female Connectors

Hardware

Warranty

Lifetime

Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Fire Rating	CMG Rated (General Purpose)

Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	5 - BNC (RF Coax)

Special Notes / Requirements

Note	RGB signal: Red, Green, Blue wires, Vertical Sync: Black wire, Horizontal Sync: White wire
------	--

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	1.0 ft [0.3 m]
Cable OD	0.3 in [8.5 mm]
Product Length	12.0 in [30.5 cm]
Product Width	1.3 in [3.3 cm]
Product Height	0.6 in [1.5 cm]
Weight of Product	3.6 oz [103.0 g]

Packaging Information

Package Quantity	1
Package Length	8.9 in [22.5 cm]
Package Width	4.9 in [12.5 cm]
Package Height	0.7 in [1.7 cm]
Shipping (Package) Weight	3.8 oz [108.0 g]

What's in the Box

Included in Package 1 - 1 ft Coax HD15 VGA to 5 BNC RGBHV Monitor Cable - M/F

****Product appearance and specifications are subject to change without notice.***