

Product information

44 21 J11

- Solid style, forged
- Non-slip, solid tips
- DIN 5256 D; 90° angled jaws
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened

Circlip Pliers

For internal circlips in bore holes

DIN 5256 D



90°

General

Article No.	44 21 J11
EAN	4003773022886
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	88 g
Dimensions	130 x 48 x 12 mm
Standard	DIN 5256 D
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Size of bore	Ø 12 – 25 mm
Tips (diameter)	Ø 1.3 mm

technical change and errors excepted