

Product information

44 21 J41

- Solid style, forged
- Non-slip, solid tips
- DIN 5256 D; 90° angled jaws
- Pliers body and tips: chrome vanadium steel, forged, oil-hardened

Circlip Pliers

For internal circlips in bore holes

DIN 5256 D



90°

General	
Article No.	44 21 J41
EAN	4003773043683
Pliers	black atramentized
Head	polished
Handles	plastic coated
Weight	462 g
Dimensions	300 x 47 x 12 mm
Standard	DIN 5256 D
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Size of bore	Ø 85 – 140 mm
Tips (diameter)	Ø 3.2 mm

technical change and errors excepted