

Product information

49 11 A3

Precision Circlip Pliers

For external circlips on shafts

DIN 5254 A



- Heavy duty in continuous operation: up to 10 times longer service life compared to turned tips
- With inserted tips for reliable work
- Large contact faces on the tips: no distortion of circlips, easy fitting
- Bolted joint: precise, zero backlash operation of pliers
- Internal opening spring, protected and captive
- Non-slip plastic coating on the handles
- DIN 5254 A; straight jaws
- Inserted tips: spring steel wire, drawn
- Pliers body: chrome vanadium electric steel, forged, oil-hardened

MM Ø



General

| | |
|-----------------|-------------------------------|
| Article No. | 49 11 A3 |
| EAN | 4003773048749 |
| Pliers | grey atramentized |
| Handles | with non-slip plastic coating |
| Weight | 270 g |
| Dimensions | 225 x 49 x 14 mm |
| Standard | DIN 5254 A |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|-----------------|---------------|
| Size of shaft | Ø 40 – 100 mm |
| Tips (diameter) | 2.3 mm |

technical change and errors excepted



Spring inside the joint: the spring is protected inside the precisely bolted joint. It does not hinder work and cannot get dirty or lost.