

Product information

02 05 180

High Leverage Combination Pliers

DIN ISO 5746



- 35 % less effort required than with conventional combination pliers
- With cutting edges (hardness approx. 63 HRC) for heavy duty
- Easier work due to optimised leverage
- Easier cutting, powerful gripping, bending and pulling
- Long cutting edges for thicker cables
- With gripping zones for flat and round material, suitable for versatile use
- Precise, minimal light gap between the gripping jaws to ensure optimal function of the cutting edges
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 63 HRC
- High-grade special tool steel, forged, multi stage oil-hardened



General

| | |
|-----------------|----------------------------|
| Article No. | 02 05 180 |
| EAN | 4003773043072 |
| Pliers | chrome-plated |
| Head | chrome-plated |
| Handles | with multi-component grips |
| Weight | 238 g |
| Dimensions | 180 x 50 x 22 mm |
| Standard | DIN ISO 5746 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|--|----------------------|
| Cutting capacities hard wire (diameter) | Ø 2.5 mm |
| Cutting capacities piano wire (diameter) | Ø 2.0 mm |
| Cutting capacity copper cable, multiple-stranded | Ø 11.5 mm |
| Cutting capacity copper cable, multiple-stranded | 16.0 mm ² |

technical change and errors excepted

