

Product information

83 30 010

Pipe Wrench S-Type

DIN 5234

- Slim, S-type jaw
- Jaws with offset teeth in opposite direction
- Teeth additionally induction-hardened
- Three-point contact on pipes, self-locking
- I-beam handle design
- Captive adjusting nut
- Red powder-coated, jaws bright ground
- Gripping jaws with specially hardened teeth, hardness approx. 56 HRC
- Chrome vanadium electric steel, forged, multi stage oil-hardened



General	
Article No.	83 30 010
EAN	4003773014249
Pliers	red powder-coated
Weight	836 g
Dimensions	320 x 59 x 20 mm
Standard	DIN 5234
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Clamping width	42 mm
Capacities for pipes (diameter)	Ø 1 5/8 Inch
Capacities for nuts	42 mm
Inner diameter, inches	Ø 1 Inch

technical change and errors excepted