

Product information

03 05 180

Combination Pliers

DIN ISO 5746

- With gripping zones for flat and round material, suitable for versatile use
- With cutting edges for soft and hard wire
- Long cutting edges for thicker cables
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 60 HRC
- Special tool steel, forged, multi stage oil-hardened



General	
Article No.	03 05 180
EAN	4003773034933
Pliers	chrome-plated
Head	chrome-plated
Handles	with multi-component grips
Weight	254 g
Dimensions	180 x 52 x 21 mm
Standard	DIN ISO 5746
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacities medium hard wire (diameter)	Ø 3.4 mm
Cutting capacities hard wire (diameter)	Ø 2.2 mm
Cutting capacity copper cable, multiple-stranded	Ø 12.0 mm
Cutting capacity copper cable, multiple-stranded	16.0 mm ²

technical change and errors excepted



