

# NSYSFNC166

Bottom and top frame, PanelSeT SFN, for electrical enclosure W1600 D600mm, roof included



## Main

Range	PanelSeT
Accessory / separate part category	Enclosure accessory
Application	Multi-purpose
Product or component type	Framework kit
For enclosure nominal dimensions	- H: 2000 mm W: 1600 mm D: 600 mm
Mounting location	Bottom of vertical uprights Top of vertical uprights
Range compatibility	PanelSeT PanelSeT SFN
Device composition	1 bottom frame 1 roof 1 top frame
Quantity per set	Set of 1

## Complementary

Material	Steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Fixing mode	By screws - each corner of enclosure location
Height	110 mm
Width	1600 mm
Depth	600 mm

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	161 cm
Package 1 Width	61 cm
Package 1 Length	15 cm
Package 1 Weight	28.5 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	12
Package 2 Height	120 cm
Package 2 Width	200 cm
Package 2 Length	80 cm
Package 2 Weight	374.1 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)  EU RoHS Declaration
Mercury free	Yes

---

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---