



## Main

|                                    |                                                                                                                               |
|------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Range                              | PanelSeT                                                                                                                      |
| Accessory / separate part category | Enclosure accessory                                                                                                           |
| Product or component type          | Door                                                                                                                          |
| Application                        | Multi-purpose                                                                                                                 |
| For enclosure nominal dimensions   | - H: 2200 mm W: 1000 mm                                                                                                       |
| Mounting location                  | Front                                                                                                                         |
| Range compatibility                | PanelSeT PanelSeT SFN                                                                                                         |
| Device composition                 | 1 door<br>1 lock with handle and 5 mm double bar insert<br>1 locking bar system 4 points<br>4 hinges<br>4 locking bar catches |
| Quantity per set                   | Set of 1                                                                                                                      |

## Complementary

|                   |                                          |
|-------------------|------------------------------------------|
| Material          | Door: Securit glass<br>Door: sheet steel |
| Colour            | Grey (RAL 7035)                          |
| Surface finish    | Epoxy-polyester powder                   |
| Lock type         | Lock 5 mm double bar                     |
| Number of locks   | 1                                        |
| Door type         | External transparent                     |
| Door opening side | Reversible (120 °)                       |
| Height            | 2166 mm nominal:                         |
| Width             | 969 mm nominal:                          |
| Net weight        | 36 kg                                    |

## Environment

|                         |      |
|-------------------------|------|
| IK degree of protection | IK08 |
|-------------------------|------|

## Packing Units

|                              |        |
|------------------------------|--------|
| Unit Type of Package 1       | PCE    |
| Number of Units in Package 1 | 1      |
| Package 1 Height             | 220 cm |
| Package 1 Width              | 98 cm  |
| Package 1 Length             | 6 cm   |
| Package 1 Weight             | 33 kg  |
| Unit Type of Package 2       | P2M    |
| Number of Units in Package 2 | 10     |
| Package 2 Height             | 120 cm |
| Package 2 Width              | 223 cm |
| Package 2 Length             | 77 cm  |
| Package 2 Weight             | 365 kg |

## Offer Sustainability

|                            |                                                                                                |
|----------------------------|------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                          |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                              |
| REACH free of SVHC         | Yes                                                                                            |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a> |
| Mercury free               | Yes                                                                                            |
| China RoHS Regulation      | <a href="#">China RoHS Declaration</a>                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                            |
| Circularity Profile        | No need of specific recycling operations                                                       |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|