



## Main

Range	PanelSeT
Accessory / separate part category	Enclosure accessory
Product or component type	Door
Application	Multi-purpose
For enclosure nominal dimensions	- H: 2200 mm W: 600 mm
Mounting location	Side Front
Range compatibility	PanelSeT PanelSeT SFN
Device composition	1 door 1 lock with handle and 5 mm double bar insert 1 locking bar system 4 points 4 hinges 4 locking bar catches
Quantity per set	Set of 1

## Complementary

Material	Door: Securit glass Door: sheet steel
Colour	Grey (RAL 7035)
Surface finish	Epoxy-polyester powder
Lock type	Lock 5 mm double bar
Number of locks	1
Door type	External transparent
Door opening side	Reversible (120 °)
Height	2166 mm nominal:
Width	569 mm nominal:
Net weight	33.3 kg

## Environment

IK degree of protection	IK08
-------------------------	------

## Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	220 cm
Package 1 Width	58 cm
Package 1 Length	6 cm
Package 1 Weight	23 kg
Unit Type of Package 2	P2M
Number of Units in Package 2	10
Package 2 Height	120 cm
Package 2 Width	230 cm
Package 2 Length	72 cm
Package 2 Weight	232 kg

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
RoHS exemption information	<a href="#">Yes</a>
Circularity Profile	No need of specific recycling operations

## Contractual warranty

Warranty	18 months
----------	-----------