

INTRODUCTION

This is a CE-certified XT60 plug that is mini-sized .The plug features a true gold plating and a banana cross recessed design with a larger contact area that can withstand a constant 30A peak current of 60A.Its plastic casing is made of insulating material, and its flame retardant grade has reached UL94 V0. It is not easy to burn after fire, and it is automatically extinguished when it leaves the fire source.The internal banana insert and the plastic case are integrally casted, and the combination is tight and resistant to plugging.At the same time, it adopts the design of special-shaped sheath, groove card slot, non-slip plug and waterproof steam, and has humanized welding joint, which has high integration degree and is convenient for welding and plugging.

FEATURES

- Non-flammable, low resistance, mini size

SPECIFICATION

- Type:XT60
- Rated voltage:DC500V
- Rated current: 30A
- Instantaneous current: 60A
- Insulation shell material: PA
- Metal head material: copper plated
- Flame retardant rating: UL94 V0
- Recommended wire gauge: 12AWG
- Contact resistance: 0.55 milliohm
- Number of uses: 1000 times
- Working environment temperature: -20 ° C ~ 120 ° C
- Safety certification: UL/CE

SHIPPING LIST

- High Quality Gold Plated XT60 Male & Female Bullet Connector x1