





Powered by BOSCH

18V 8.0 Ah battery AMPShare Alliance from BOSCH 350°C

< 4 Sek. Temperature Boost 1000 W

Power

150°C - 550°C

Digitally controlled temperature levels

200 l/min

Automatic air flow



Suitable for screwable nozzles



Temperature adjustment in 9 steps



Status LED for temperature



On-Off switch: with permanent switch-on



Non-slip standing

The series at a glance

 ${\cal I}$

Proven for craft fans and DIY enthusiasts

-

Professional craftsmen who work quickly & flexibly

7

For the daily continuous use of heavy users

The right choice for am-

bitious do-it-yourselfers



Powered by







Technical data

Connection	8.0 Ah battery (AMPShare)
Heating time	<4 seconds
Temperature	150 - 550 °C
Battery runtime	10 min

Article

MH 7 incl. battery and charger		
in a practical case	4007841 085933	

















