

Product information

00 21 06

Tool Case "BIG Basic Move" ElectricPlus

68 parts



- Equipped with 27 KNIPEX tools, a total of 68 brand tools, partly VDE-tested according to DIN EN 60900
- Telescopic handle set in the base as well as two external, smooth-running skater wheels
- Two metal flip locks and a three-digit combination lock for secure locking of the cover
- Label field with two stickers for individual labelling
- Max. payload: 20 kg
- Volume: 33 litres
- Strong, ergonomic handle
- Heavy duty ABS material, black
- Circumferential aluminium frame
- Metal hinges
- Document compartment in the cover
- Two removable tool boards made of dirt-repellent PP twin-fall sheets with 31 tool pockets
- Base tray, can be fixed by a push button, 70 mm high, can be subdivided by inserts, cover board with 14 large tool pockets
- With a total of 54 inserting options














General





















Article No.	00 21 06
EAN	4003773086260
Weight	11,590 g
Dimensions	438 x 265 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Dimension exterior (interior) width mm	430 mm (350 mm)
Dimension exterior (interior) height mm	280 mm (200 mm)
Dimension exterior (interior) depth mm	515 mm (480 mm)

Content

00 11 01	1 x KNIPEX TwinKey® Control Cabinet Key for all standard cabinets and shut-off systems
08 26 145	1 x Needle-Nose Combination Pliers   
12 52 195	1 x KNIPEX PreciStrip16 Automatic Insulation Stripper (0,08 - 16 mm ²)
13 86 200	1 x Pliers for Electrical Installation (Ø 15 mm / 50 mm ²)    
16 95 01 SB	1 x KNIPEX ErgoStrip® Universal Stripping Tool for right-handers (Ø 8,0 – 13,0 mm) 
26 26 200	1 x Snipe Nose Side Cutting Pliers (Stork Beak Pliers)     

Content	
70 06 160	1 x Diagonal Cutter ⚡1000V 
74 06 200	1 x High Leverage Diagonal Cutter ⚡1000V 
78 06 125	1 x Electronic Super Knips® VDE ⚡1000V 
87 01 180	1 x KNIPEX Cobra® High-Tech Water Pump Pliers 
97 53 18	1 x KNIPEX Twistor®16 Self-Adjusting Crimping Pliers for wire ferrules with rotatable die head (0,14 – 16 mm ²) 
98 20 25	1 x Screwdrivers for slotted screws (2,5 mm) ⚡1000V 
98 20 35 SL	1 x Screwdriver (Slim) for slotted screws (3,5 mm) ⚡1000V 
98 20 40 SL	1 x Screwdriver (Slim) for slotted screws (4,0 mm) ⚡1000V 
98 20 55 SL	1 x Screwdriver (Slim) for slotted screws (5,5 mm) ⚡1000V 
98 24 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH1) ⚡1000V 
98 24 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Phillips® (PH2) ⚡1000V 
98 25 01 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 1) ⚡1000V 
98 25 01 SLS	1 x (Slim) PlusMinus screwdriver Pozidriv® (PZ/S 1) ⚡1000V 
98 25 02 SL	1 x Screwdriver (Slim) for cross-recessed screws Pozidriv® (PZ 2) ⚡1000V 
98 25 02 SLS	1 x (Slim) PlusMinus screwdriver Pozidriv® (PZ/S 2) ⚡1000V 
98 26 10	1 x (TX10) ⚡1000V 
98 26 15	1 x (TX15) ⚡1000V 
98 26 20	1 x (TX20) ⚡1000V 
98 26 25	1 x (TX25) ⚡1000V 
98 26 30	1 x (TX30) ⚡1000V 
L240 00055	1 x Knipex Folding ruler Stabila series 400 (200 mm)
101-0300	1 x Picard Locksmith's hammer (300 g)
361 252 1	1 x Rennsteig Electrician's Chisel (250 x 10 mm)
16135	1 x Stabila Spirit Level Type 70 Electric (430 mm)
18115	1 x Stabila Pocket Electric mini spirit level (68 mm)
0022086	1 x Wera set of hex key wrenches (1,5 - 10 mm)
004018	1 x Wera 8100 SA 8 Zyklop set of metal ratchets 28 parts (1/4")

Accessories

00 21 06 LE

Tool Case "BIG Basic Move" empty,

technical change and errors excepted

