

Glue sticks Ø 11 mm PUR

5 Stk.
 EAN 4007841 087395
 Article number 087395



130°C



Lösemittelfrei

Function description

Our innovation: The outdoor hot glue stick PUR! Experience the power and durability your projects need with the Ø 11 mm glue stick PUR. The polyurethane adhesive is weather and moisture resistant and lasts permanently. It's the ideal solution for projects that require high temperature resistance and a reliable, long-lasting bond, even in extreme conditions like outdoors. It's great for a variety of materials, including wood, plastic, metal and more. Whether for craft projects, repairs or industrial applications. With our hot glue guns MG 3011, MG 5011 and the GM 7011, its low processing temperature of 130 °C can be adjusted, it is solid after max 25 seconds and loadable after about 50 seconds, final strength after 72 hrs. Important note on use: At the end of application of the polyurethane adhesive or after 8 h at the latest, clean the glue gun with the rinsing agent stick.

Technical specifications

Suitable for	Sheetings, Glass, Rubber, Rigid PVC, Wood, Rubber (CR), ceramic, Leather, Metal, Paper, Paper, lacquered, Card / cardboard boxes, PET, Tarpaulins, Plexiglas®, PP, PVC, Polystyrene, Textiles	Solvent-free	Yes
		PU1, net weight	0,15 kg
Melt temperature	130 °C	Manufacturer's Warranty	1 year
Glue reaches final strength after:	72 h	PU1, EAN	4007841087395
Open time	25 sec		
Setting time	50 sec		

Accessories

EAN 4007841 087401	Cleaning stick 5 pcs (100g)
EAN 4007841 075965	Long nozzle 2.8 mm
EAN 4007841 076160	Fine nozzle 1.0 mm