

Product Search Data Sheet

Note: This datasheet may be out of date. Please download the latest datasheet of GRM319R61E106KA12# from the official website of Murata Manufacturing Co., Ltd.

"#" indicates a package specification code.

http://www.murata.com/en-gb/products/productdetail?partno=GRM319R61E106KA12%23

References

Specifications

φ180mm Reel Paper Tape

φ330mm Reel Paper Tape

24.0mg

Packaging

Mass (typ.)

1 piece

D

J

GRM319R61E106KA12D




< List of part numbers with package codes > GRM319R61E106KA12D GRM319R61E106KA12J

Applications

Unsuitable	Please be sure to read and comply with
Applications	these "Precautions for use."
Specific Applications	Consumer equipment,Industrial Equipment,Mobile Electronics,Medical equipment [GHTF A/B/C] except for implant equipment,Automotive infotainment/comfort equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.

Appearance & Shape





1 of 2

Standard

Packing Quantity

4000

10000

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.





GRM319R61E106KA12D

Note: This datasheet may be out of date. Please download the latest datasheet of GRM319R61E106KA12# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en-gb/products/productdetail?partno=GRM319R61E106KA12%23

"#" indicates a package specification code.



Specifications

Length	3.2±0.15mm
Width	1.6±0.15mm
Thickness	0.85±0.1mm
Capacitance	10µF ±10%
Distance between external terminals g	1.5mm min.
External terminal size e	0.3 to 0.8mm
Operating Temperature Range	-55°C to 85°C
Rated Voltage	25Vdc
Size code in inch(mm)	1206 (3216M)
Capacitance change rate	±15.0%
Temperature characteristics (complied standard)	X5R(EIA)
Temperature range of temperature characteristics	-55℃ to 85℃

2 of 2

Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued

without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

