

Product data sheet

✉ sales@brannan.co.uk

☎ +44 (0)1946 816600

🌐 brannan.co.uk

STAINLESS STEEL WATER RESISTANT TEST THERMOMETER

Max-min thermometer with 125mm stainless steel probe.
Supplied with protective cover and hanging clip.

Product features:

- Max/min memory
- Robust 125mm stainless steel probe
- Protective plastic case and hanging hook
- Full operating instructions and battery included

Product specifications:

Temperature range:	-10 to +200°C&F
Operating temperature:	0 to +40°C&F
Divisions:	0.1°C
Accuracy:	-10 to +40°C: ± 2°C, +41 to +70°C: ± 3°C, +71 to +130°C: ± 5°C, +131 to +160°C: ± 6°C, +161 to +200°C: ± 8°C
Sampling rate:	After approx 11-12 seconds
CE and ROHS/WEEE:	Compliant
Hazard information (SDS):	See brannan.co.uk for information
Battery:	1 x AAA (approx life - 2 yrs)
LCD dimensions:	12mm x 30mm
Probe dimensions:	125mm x 4mm diameter
Product dimensions:	Net: 280mm x 40mm x 38mm Gross: 318mm x 48mm x 35mm
Product weight:	Net: 68g Card packaging: 25.5g Gross: 93.5g



Description	Barcode	Product No
Catering Test Thermometer	5 011405 311573	31/157/0

View me on
the website

