

# ROLINE GOLD USB 2.0 Cable, reversible A - C 90° angled, M/M, 0.8 m

<b>Product No.</b>	11.02.9060
<b>Manufacturer</b>	ROLINE
<b>Manufacturer No.</b>	11.02.9060
<b>EAN (single piece)</b>	7630049615748



**USB 2.0 connection cable in ROLINE GOLD quality with high quality shielding. Gilded contacts for contact safety even at high plug-in cycles.**

USB 2.0 Hi-Speed cable with high quality and improved shielding.

- For the connection of devices with USB Type C connector; e.g. smartphones / mobile phones or digital cameras / DSLR
- Improved shielding
- The plugs are gold coated to enhance their contact durability
- Nylon-reinforced outer material for a better stability
- Supports data transfer rates of up to 480 Mbit/s
- High quality USB cable with one Type A and one type C USB connector (90° angled)
- Meets standard USB 2.0 (transfer rate up to 480 Mbit/s)
- Colour: gold and black

**ROLINE GOLD - Top quality without any compromises!**

Cables in ROLINE GOLD quality come with high quality shielding and gilded contacts for contact safety even at high plug-in cycles. The plugs are gold coated to enhance their contact durability. Nylon-reinforced outer material in golden/black provides a better stability and gives the cable a stunning look.

## Technical specifications

Manufacturer	ROLINE
--------------	--------

Product group	Cable
Product type	USB 2.0 Cable
Colour	black / gold
Length	0.8 m
Transfer quality	USB 2.0 Hi-Speed 480 Mbit/s
Connection ports	USB 2.0 Type A Male / USB Type C (USB-C) Male
side 1 connector	Type A Male
side 2 connector	Micro USB B M
Side 1 Connector Type	USB 2.0 Type A
Side 1 Connector Gender	Male
Side 2 Connector Type	USB Type C (USB-C)
Side 2 Connector Gender	Male
Area of application	External
Cable shielding	Screened
Weight	37.9 g
Height of packaging (single piece)	10 mm
Width of packaging (single piece)	50 mm
Depth of packaging (single piece)	50 mm
Package weight (single piece)	0.02 kg