

# ROLINE UTP Data Center Patch Cord Cat.6A (Class EA), LSOH, Slim, yellow, 5 m

**Product No.** 21.15.3927  
**Manufacturer** ROLINE  
**Manufacturer No.** 21.15.3927  
**EAN (single piece)** 7630049615052

**roline**  
Designed for Professionals



**Category 6A twisted-pair patch cable with RJ-45 connectors on both sides. Particularly thin and flexible cable with individual pairs of wires for use in confined spaces, such as in data centres.**

- Durable thanks to moulded-on kink protection
- Suitable as patch cable in patch panels or as device connection cable and intended for use in the LAN
- Contact assignment: 1:1 according to EIA/TIA568, 8 cores
- Structure: 8 cores stranded wire

## Technical specifications

Manufacturer	ROLINE
Product group	Twisted Pair Cable
Product type	UTP Patch Cables
Colour	yellow
Length	5 m
Shield type	UTP

Transfer quality	Cat6A / Class EA
------------------	------------------

Quantity of wires	8
-------------------	---

Conductor type	Wire
----------------	------

Crossed	No
---------	----

Slim cable	Yes
------------	-----

External cable diameter	3.4 +/- 0.2mm
-------------------------	---------------

Cable LSOH	Yes
------------	-----

Side 1 Connector Type	RJ-45
-----------------------	-------

Side 1 Connector Gender	Male
-------------------------	------

Side 2 Connector Type	RJ-45
-----------------------	-------

Side 2 Connector Gender	Male
-------------------------	------

Connector Type RJ45	Standard
---------------------	----------

Operating temperature min.	-10 °C
----------------------------	--------

Operating temperature max.	60 °C
----------------------------	-------

Weight	70 g
--------	------

Height of packaging (single piece)	10 mm
------------------------------------	-------

Width of packaging (single piece)	100 mm
-----------------------------------	--------

Depth of packaging (single piece)	100 mm
-----------------------------------	--------

Package weight (single piece)	0.01 kg
-------------------------------	---------