

# ROLINE UTP Data Center Patch Cord Cat.6A (Class EA), LSOH, Slim, green, 3 m

**Product No.** 21.15.3936  
**Manufacturer** ROLINE  
**Manufacturer No.** 21.15.3936  
**EAN (single piece)** 7630049615120

**roline**  
Designed for Professionals



**Category 6A twisted-pair patch cable with RJ-45 connectors on both sides. Particularly thin and flexible cable with individual pairs of wires for use in confined spaces, such as in data centres.**

- Durable thanks to moulded-on kink protection
- Suitable as patch cable in patch panels or as device connection cable and intended for use in the LAN
- Contact assignment: 1:1 according to EIA/TIA568, 8 cores
- Structure: 8 cores stranded wire

## Technical specifications

|               |                    |
|---------------|--------------------|
| Manufacturer  | ROLINE             |
| Product group | Twisted Pair Cable |
| Product type  | UTP Patch Cables   |
| Colour        | green              |
| Length        | 3 m                |
| Shield type   | UTP                |

|                                    |                  |
|------------------------------------|------------------|
| Transfer quality                   | Cat6A / Class EA |
| Quantity of wires                  | 8                |
| Conductor type                     | Wire             |
| Crossed                            | No               |
| Slim cable                         | Yes              |
| External cable diameter            | 3.4 +/- 0.2mm    |
| Cable LSOH                         | Yes              |
| Side 1 Connector Type              | RJ-45            |
| Side 1 Connector Gender            | Male             |
| Side 2 Connector Type              | RJ-45            |
| Side 2 Connector Gender            | Male             |
| Connector Type RJ45                | Standard         |
| Operating temperature min.         | -10 °C           |
| Operating temperature max.         | 60 °C            |
| Weight                             | 43.4 g           |
| Height of packaging (single piece) | 10 mm            |
| Width of packaging (single piece)  | 150 mm           |
| Depth of packaging (single piece)  | 160 mm           |
| Package weight (single piece)      | 0.052 kg         |