ROLINE UTP Data Center Patch Cord Cat.6A (Class EA), LSOH, Slim, blue, 0.15 m

Product No. 21.15.3940

rollne

Manufacturer

ROLINE


Manufacturer No.

21.15.3940

EAN (single piece)

7630049615144















Category 6A twisted-pair patch cable with RJ-45 connectors on both sides. Particularly thin and flexible cable with individual pairs of wires for use in confined spaces, such as in data centres.

- Durable thanks to moulded-on kink protection
- Suitable as patch cable in patch panels or as device connection cable and intended for use in the LAN
- Contact assignment: 1:1 according to EIA/TIA568, 8 cores
- Structure: 8 cores stranded wire

| Technical specifications | | |
|--------------------------|--------------------|--|
| Manufacturer | ROLINE | |
| Product group | Twisted Pair Cable | |
| Product type | UTP Patch Cables | |
| Colour | blue | |
| Length | 0.15 m | |
| Shield type | UTP | |

| Transfer quality | Cat6A / Class EA |
|------------------------------------|------------------|
| Quantity of wires | 8 |
| Conductor type | Wire |
| Crossed | No |
| Slim cable | Yes |
| External cable diameter | 3.4 +/- 0.2mm |
| Cable LSOH | Yes |
| Side 1 Connector Type | RJ-45 |
| Side 1 Connector Gender | Male |
| Side 2 Connector Type | RJ-45 |
| Side 2 Connector Gender | Male |
| Connector Type RJ45 | Standard |
| Operating temperature min. | -10 °C |
| Operating temperature max. | 60 °C |
| Weight | 7.2 g |
| Height of packaging (single piece) | 10 mm |
| Width of packaging (single piece) | 20 mm |
| Depth of packaging (single piece) | 20 mm |
| Package weight (single piece) | 0.01 kg |