

Han-INOX® 16B-HTE-M32 f.DL



Image is for illustration purposes only. Please refer to product description.

| | |
|---------------|----------------------------|
| Part number | 19 44 016 0427 |
| Specification | Han-INOX® 16B-HTE-M32 f.DL |

Identification

| | |
|--------------------------|----------------|
| Category | Hoods/Housings |
| Series of hoods/housings | Han-INOX® |
| Type of hood/housing | Hood |

Version

| | |
|----------------------|---------------------------------------|
| Size | 16 B |
| Version | Top entry |
| Cable entry | 1x M32 |
| Locking type | Double locking lever |
| Field of application | Hoods/housings for harsh environments |

Technical characteristics

| | |
|--|--|
| Limiting temperature | -40 ... +125 °C |
| Note on the limiting temperature | For use as a connector according to IEC 61984. |
| Degree of protection acc. to IEC 60529 | IP65 |
| Type rating acc. to UL 50 / UL 50E | 4 4X 12 |

Material properties

| | |
|-------------------------|-----------------|
| Material (hood/housing) | Stainless steel |
| Surface (hood/housing) | Uncoated |
| Colour (hood/housing) | Unpainted |
| RoHS | compliant |



Pushing Performance
Since 1945

Material properties

| | |
|--------------------------------------|---------------|
| ELV status | compliant |
| China RoHS | e |
| REACH Annex XVII substances | Not contained |
| REACH ANNEX XIV substances | Not contained |
| REACH SVHC substances | Not contained |
| California Proposition 65 substances | Not contained |

Specifications and approvals

| | |
|-----------|--|
| UL / CSA | UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076 |
| CE | Yes |
| Approvals | DNV GL |

Commercial data

| | |
|--------------------------------|--|
| Packaging size | 1 |
| Net weight | 654.1 g |
| Country of origin | Romania |
| European customs tariff number | 85389099 |
| ETIM | EC000437 |
| eCl@ss | 27440202 Shell for industrial connectors |