

Han-INOX® 10B-C-f. DL



Image is for illustration purposes only. Please refer to product description.

Part number	19 44 010 5405
Specification	Han-INOX® 10B-C-f. DL
HARTING eCatalogue	https://b2b.harting.com/19440105405

Identification

Category	Accessories
Series of hoods/housings	Han-INOX®
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings Metal With fixing cord (cable shoe)

Version

Size	10 B
Locking type	Double locking lever

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

Material properties

Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained



Pushing Performance
Since 1945

Material properties

REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Approvals	DNV GL
-----------	--------

Commercial data

Packaging size	1
Net weight	125 g
Country of origin	Romania
European customs tariff number	85389099
ETIM	EC002314
eCl@ss	27440208 Cap for industrial connectors