

1.6ft (50cm) Rugged Right Angle USB-C Cable, USB 3.2 Gen 2 (10 Gbps), Full-Featured USB C to C Data transfer Cable, 4K 60Hz DP Alt Mode, 100W Power Delivery - 90 Degree USB Type-C Cable

Product ID: RUSB31CC50CMBR



Connect USB 10 Gbps source and peripheral devices, using this 1.6ft (50cm) Rugged Right Angle USB Type-C Cable. Position the right angle USB-C connection along the device to reduce cable clutter and avoid prolonged strain from bending.

It is ideal for 10 Gbps data transfer to external USB-C-enabled external storage devices, or as a single-cable connection from a USB-C dock to a laptop.

The Rugged USB-C cable supports up to 4K 60Hz video over DisplayPort 1.2 Alt Mode, and is compatible with 1080p and lower resolutions.

Designed to withstand heavy use, the USB-C cable features an Aramid fiber core and durable TPE outer jacket. This heavy-duty construction protects against fraying or breakage and resists tangling.

This USB Type-C cable features Power Delivery (PD) 3.0 with up to 100W PD output. Power and charge a USB-C laptop, such as Apple MacBook, Lenovo ThinkPad, or Microsoft Surface with up to 100W output over USB Power Delivery 3.0. Connect the USB-C cable from a laptop to a USB-C wall charger or docking station.

Certifications, Reports and Compatibility



Applications

Features

- **RIGHT ANGLE USB CABLE:** Rugged USB Type-C Cable features a right angle USB-C connector; Ideal for connecting in tight spaces; 90 degree connector optimizes cable routing without placing unnecessary strain on the connector and device
- **DURABLE CONSTRUCTION:** The USB-C cable is reinforced with Aramid fiber to enhance flexibility and protection from frequent bending and wear; Robust strain reliefs with 8mm bend radius; Nickel-plated connectors rated beyond 10,000 insertion cycles
- **FULL-FEATURE USB-C:** Right angle USB-C cable supports up to 10 Gbps transfer rates, 4K 60Hz DP Alt Mode, and 100W Power Delivery; Universal compatibility between USB-C laptops, docking stations, UHD monitors, and external devices
- **THOUGHTFUL DESIGN:** Built-in E-Marker chip for consistent data, video, and Power Delivery output; Flexible TPE outer jacket is nontoxic, halogen-free, and RoHS compliant; Aluminum-mylar shield for enhanced EMI protection
- **PERFORMANCE:** USB 3.2 Gen 2 (10 Gbps); 4K 60Hz DP Alt Mode 1.2; 100W Power Delivery; 1.6ft (50cm); Black; 4.8mm O.D.; Dock and charge a USB-C laptop over a single connection; Optimize cable routing to a USB-C device

Hardware

| | |
|---------------------------|--------------------------------|
| Warranty | 2 Years |
| Active or Passive Adapter | Passive |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |

Performance

| | |
|-----------------------------|---------------------------|
| Video Revision | DisplayPort 1.2 |
| Maximum Cable Length | 1.6 ft [0.5 m] |
| Maximum Digital Resolutions | 4K 60Hz |
| Type and Rate | USB 3.2 Gen 2 - 10 Gbit/s |

Connector(s)

| | |
|-------------|---|
| Connector A | 1 - USB 3.2 Gen 2 USB Type-C (Power Delivery + Data, 24 Pin, 10 Gbps) |
| | 1 - USB 3.2 Gen 2 USB Type-C (Power Delivery + Data, 24 Pin, 10 Gbps) |

Power

| | |
|----------------|------|
| Power Delivery | 100W |
|----------------|------|

Environmental

| | |
|-----------------------|---------------------------|
| Operating Temperature | 0C to 50C (32F to 122F) |
| Storage Temperature | -20C to 60C (-4F to 140F) |
| Humidity | 0%~85% RH |

Physical Characteristics

| | |
|-------------------|-------------------------|
| Color | Black |
| Connector Style | Right Angle to Straight |
| Cable Length | 19.7 in [50 cm] |
| Cable OD | 0.2 in [4.8 mm] |
| Product Length | 19.7 in [50.0 cm] |
| Product Width | 1.0 in [2.6 cm] |
| Product Height | 0.2 in [6.3 mm] |
| Weight of Product | 0.9 oz [25.0 g] |

Packaging Information

| | |
|---------------------------|------------------|
| Package Quantity | 1 |
| Package Length | 5.0 in [12.8 cm] |
| Package Width | 8.7 in [22.0 cm] |
| Package Height | 0.6 in [1.4 cm] |
| Shipping (Package) Weight | 1.1 oz [30.0 g] |

What's in the Box

| | |
|---------------------|-----------------------------------|
| Included in Package | 1 - 50cm Right Angled USB-C Cable |
|---------------------|-----------------------------------|

**Product appearance and specifications are subject to change without notice.*