

1993 U-20

1/2" Reversible ratchet

Code	ETIM
1436686	EC002218
EAN	UNSPSC
4010886805558	27-11-17-11
Country of origin	eCl@ss
Germany	21-04-02-08
Customs tariff number	
82041100	



Article description

- Used throughout industry and the automotive world - and as well in confined spaces
- Acc. to DIN 3122, ISO 3315
- Small, drop shaped head for confined spaces
- Fine-toothed (60 teeth), with lever change and push-button release
- Return angle 6°
- Non-slip 2-component handle with hanging hole
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 12.5, ISO 1174, ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated

Article information

Contents (Qty of pieces)	1	Return angle	6°
Total length [mm]	275 mm	Drive connector square (male)	1/2"
Material	Chrome-vanadium steel 31CrV3	Drive connector square (male)	12,5 mm
Surface	chrome-plated	Ratchet head height	37,5 mm
Net weight [kg]	0,536 kg	Number of teeth	60
Total width [mm]	40 mm	Locking type	Ball locking device
Total height [mm]	38 mm	Push button release	yes
Standard	DIN 3122 ISO 3315	Shift type	Changeover lever
Handle material	2-components		