

VDE 8132 AB-160 H

VDE Telephone pliers

with VDE insulating sleeves, angled pattern

Code	ETIM
1552139	EC000834
EAN	UNSPSC
4010886816035	27-11-21-25
Country of origin	eCl@ss
Austria	21-04-03-01
Customs tariff number	
82032000	



Article description

- Long, flat-round jaws, straight gripping faces, serrated
- 45° angled tips make gripping round the corner possible
- Induction-hardened precision cutting edges, hardness 61 - 63 HRC
- GEDORE special hardened and tempered steel, drop-forged, oil-hardened and annealed
- Handles with VDE insulating sleeves up to 1000 V, acc. to EN 60900/IEC 60900

Article information

Contents (Qty of pieces)	1	Jaw length L3 [mm]	46 mm
Total length [mm]	160 mm	Head thickness [mm] T1	9,0 mm
Material	Heat-treated steel	Design non-sparking	No
Handle design	2-component grips VDE insulated up to 1000 V.	with cutting edge	yes
Surface	chrome-plated	Hardness of cutting edge	61 - 63 HRC
Net weight [kg]	0,173 kg	Width of centres W4 [mm]	3,2 mm
Total width [mm]	54 mm	Thickness of point	2,5 mm
Total height [mm]	26 mm	reversible arms available	no
Width of head l [mm]	16,5 mm	Clamping bracket available	no
Standard	DIN ISO 5745 EN 60900/IEC60900	Cutting values	Hard wire: 1,6 mm / 14 AWG Medium hard wire: 2,5 mm / 10 AWG