

2093 U-20

1/4" Reversible ratchet

Code	ETIM
1703749	ECO02218
EAN	UNSPSC
4010886855638	27-11-17-11
Country of origin	eCl@ss
Germany	21-04-02-08
Customs tariff number	
82041100	



Article description

- Acc. to DIN 3122, ISO 3315
- Small, drop shaped head for confined areas
- Fine-toothed, with lever change and push-button release
- Return angle 9 degrees
- Non-slip 2-component handle with hanging hole
- For hand-operated sockets and accessories with square drive as per DIN 3120 - C 6.3, ISO 1174, ball locking device
- GEDORE vanadium steel 31CrV3, chrome-plated
- GEDORE vanadium steel 31CrV3, chrome-plated

Article information

Contents (Qty of pieces)	1	Return angle	9°
Total length [mm]	130 mm	Drive connector square (male)	1/4"
Material	Chrome-vanadium steel 31CrV3	Drive connector square (male)	6,3 mm
Surface	chrome-plated	Ratchet head height	20 mm
Net weight [kg]	0,095 kg	Number of teeth	40
Total width [mm]	24 mm	Locking type	Ball locking device
Total height [mm]	21 mm	Push button release	yes
Standard	DIN 3122 ISO 3315	Shift type	Changeover lever
Handle material	2-components		