

## 7 R 8

### Combination ratchet spanner

Flat pattern

Code	ETIM
2297051	ECO02176
EAN	UNSPSC
4010886889138	27-11-17-13
Country of origin	eCl@ss
Germany	21-04-01-05
Customs tariff number	
82041100	



### Article description

- With same size each end
- UD-Profile
- High torque transfer
- Chrome-vanadium steel 31CrV3
- Non-glare look due to matt chrome-plating, locking insert and pawl manganese-phosphated
- Hot forged
- Jaw: ground precisely to exact nominal size for optimum contact areas
- In combination with adaptor 7 RA or 7 RB (please order separately) the spanner 7 R can be used as a (bit) ratchet
- Hollow profile comfortable to hold
- Warp-resistant geometry with double T-girder effect
- For ratchet loosening and fast tightening
- Ring 13° offset from shaft, reversible

### Article information

Contents (Qty of pieces)	1	Head height 1 [mm]	7 mm
Total length [mm]	141 mm	Width of head 1 [mm]	17,5 mm
Material	31CrV3	Width of head 2 [mm]	19,8 mm
Surface	chrome-plated	Standard	not standardised
Net weight [kg]	0,032 kg	Head height 2 [mm]	3,8 mm
Total width [mm]	20 mm	Jaw set	15°
Total height [mm]	7 mm	Return angle	7°
Width across flats [mm]	8,0		