

7 R 10

Combination ratchet spanner

Flat pattern

Code	ETIM
2297086	ECO02176
EAN	UNSPSC
4010886889169	27-11-17-13
Country of origin	eCl@ss
Germany	21-04-01-05
Customs tariff number	
82041100	



Article description

- With same size each end
- UD-Profile
- High torque transfer
- Chrome-vanadium steel 31CrV3
- Non-glare look due to matt chrome-plating, locking insert and pawl manganese-phosphated
- Hot forged
- Jaw: ground precisely to exact nominal size for optimum contact areas
- In combination with adaptor 7 RA or 7 RB (please order separately) the spanner 7 R can be used as a (bit) ratchet
- Hollow profile comfortable to hold
- Warp-resistant geometry with double T-girder effect
- For ratchet loosening and fast tightening
- Ring 13° offset from shaft, reversible

Article information

Contents (Qty of pieces)	1	Width across flats [mm]	10
Total length [mm]	160 mm	Head height 1 [mm]	7,7 mm
Material	31CrV3	Width of head 1 [mm]	21,0 mm
Surface	chrome-plated	Width of head 2 [mm]	23 mm
Net weight [kg]	0,054 kg	Standard	not standardised
Total width [mm]	24 mm	Head height 2 [mm]	4,1 mm
Total height [mm]	8 mm	Jaw set	15 °
Width across flats 1 [mm]	10	Return angle	7 °