

CD Tuners

MD Tuners

Radio CD, Radio MD	CDX-L480X	CDX-L380X	CDX-L420V	MDX-M690	MDX-CA70
Tuner					
Tuner/ABC (Automatic Bandwidth Control)	SSIR-EXA/0	SSIR-EXA/0	SSIR-EXA/0	SSIR-EXA/0	SSIR-EXA/0
Station Presets: FM/MW/LW/SW	18/6/6/-	18/6/6/-	18/6/6/-	18/6/6/-	18/6/6/-
BTM (Best Tuning Memory)	0	0	0	0	0
RDS EON	0	0	0	0	0
Cassette					
Auto Reverse Mechanism	-	-	-	-	-
Full Logic Control	-	-	-	-	-
AMS (Automatic Music Sensor)	-	-	-	-	-
Dolby NR: B/C	-/-	-/-	-/-	-/-	-/-
Metal	-	-	-	-	-
Repeat/Blank Skip	-/-	-/-	-/-	-/-	-/-
ATA (Automatic Tuner Activation)	-	-	-	-	-
Integrated MD, CD Player					
Mechanism: MiniDisc*/Compact Disc	-/1x CD	-/1x CD	-/1x CD	1x MD/-	1x MD/-
Tray mechanism	-	-	-	-	-
MD: MDLP	-	-	-	0	0
Shock Resistant Memory	-	-	-	4 Mbit, 10 sec	4 Mbit/10
Wide Bit Stream	-	-	-	0	0
Data Compression	-	-	-	ATRAC, ATRAC3	ATRAC, AT
CD: CD-R/CD-RW Playback capability	0/0	0/0	0/0	-/-	-/-
MP3 Playback capability	-	-	-	-	-
ID3 Tag (Track-, Artist-, Album name)	-	-	-	-	-
Electronic Shock Protection	-	-	-	-	-
CD Text	0	0	0	-	-
Title Scroll: MD/CD Text	-/0	-/0	-/0	0/-	0/-
Frequency Response	10 - 20000 Hz	10 - 20000 Hz	10 - 20000 Hz	10 - 20000 Hz	10 - 20000 Hz
Signal to Noise Ratio	90 dB	90 dB	90 dB	90 dB	90 dB
Repeat/Shuffle	0/0	0/0	0/0	0/0	0/0
Changer Control					
Changer Control: CD/MD	-/-	-/-	-/-	0/0	0/0
CD Custom File Control	-	-	-	0	0
Display of: ID3 Tag (Track-, Artist-, Album name)	-	-	-	-	-
CD Text	-	-	-	0	0
List Function: CD/MD	-/-	-/-	-/-	0/0	0/0
Title Scroll: CD Text/MD	-/-	-/-	-/-	0/0	0/0
Repeat/Shuffle	-/-	-/-	-/-	0/0	0/0
Amplifier					
Output Power (DIN 45324, 4 ohm)	4x 25 W	4x 25 W	4x 25 W	4x 27 W	4x 26 W
Max. Output Power (1 kHz, 4 ohm)	4x 45 W	4x 45 W	4x 45 W	4x 52 W	4x 50 W
Dynamic Soundstage Optimiser: DSD/DSO II	-/-	-/-	-/-	0/-	-/0
EQ-7 (7-Band Equaliser)	-	-	-	0	-
EQ-3 (3-Band Equaliser)	0	-	-	-	0
My Best sound Position	-	0	0	-	-
Separate Bass, Treble Control	EQ3	0	0	0	EQ3
Loudness/D-Bass (Dynamic Bass)	-/-	-/0	-/0	0/-	-/-
Pre-amp Output: Front/Rear	-/0	-/0	-/-	0/0 (HPF)	0/0
Max. Pre-amp output level	2 V	2 V	2 V	2 V	2 V
Sub Output/Switchable Low Pass Filter	-/-	-/-	-/-	0 Mono/0	-/-
Sub Volume Control	-	-	-	0	-
AUX Input	-	-	-	-	-
Others					
DSP-Control	-	-	-	-	-
Display: 3D Fluorescent	-	-	-	-	-
Dot Matrix LCD/Segment LCD	-/0	-/0	-/0	0/-	-/0
Multi Colour/2 Colour/1 Colour	-/-/0	-/-/0	-/-/blue	0/-/blue	-/0/-
Selectable Display Colour	-	-	-	-	-
Contrast Adjustment	-	-	-	0	-
Display Dimmer	-	-	-	0	-
Key Illumination: Amber, Green switchable	red	red	red	red	red
Safety Commander Interface: 3.5 mm (gold/intermittent)	-/-	-/-	0/-	0/0 High Band	0/-
Sensor for IR Commander	0	-	-	0 High Band	0
Removable Front Panel/Security Code	0/-	0/-	0/-	0/-	0/-
Integrated Clock: 24 h/12 h	0/-	0/-	0/-	0/-	0/-
Telephone Attenuator	0	0	0	0	0
ISO Connector: Integrated/supplied Adaptor	-/0	-/0	-/0	-/0	-/0
Supplied Adaptor Cable (radio/car harness)	16pin/ISO	16pin/ISO	16pin/ISO	16pin/ISO	16pin/ISO
Installation Angle	0-60°	0-60°	0-60°	0-20°	0-30°
Dimensions (W x H x D in mm) approx.	178 x 50 x 180	178 x 50 x 177	178 x 50 x 177	178 x 50 x 182	178 x 50

0 = yes/- = no

(HPF) switchable Highpass

(1) Not available if CD/MD changer is used