



Sample photo

**Order symbol:** PC 21/18-3  
**Product nbr:** 7525154

**EAN:** 6418074056733

**Description:** Enclosure, PC  
**Remarks:** Smoked transparent cover

**Including:** Base, terminal compartment cover with EPDM gasket and screws for mounting plate/DIN-rail. -3 and -L3 versions: Smoked transparent cover with PUR gasket, hinges, locking devices; FC version: Closed PC frame front plate with PUR gasket and cover screws.

Dimensions:		L	W	H	Rating:
mm:		213	185	118	<b>Ingress Protection (EN 60529):</b> IP 65
inch:		8.4	7.3	4.6	<b>Impact Resistance (EN 50102):</b> IK 08/07
Materials:					
<b>Material:</b>		PC			
<b>Base colour:</b>		RAL 7035			
<b>Cover colour:</b>		Smoked grey			
<b>Gasket material:</b>		EPDM and Polyurethane			
Temperatures:					
<b>Short term:</b>		-40 ... 120 °C			
<b>Continuous:</b>		-40 ... 80 °C			
<b>Short term:</b>		-40 ... 250 °F			
<b>Continuous:</b>		-40 ... 175 °F			
Accessories:					
MP 21/18		Mounting plate			
FP 21/18		Front plate			
CM 21/18-3T		Cover			
SET 17/16-21/18-3		Set of hinges and latches			
Certificates:					
		<b>Underwriters Laboratories</b>			
		<b>Fimko</b>			
		<b>Europe EN 50298 1998</b>			
		<b>UL Canada</b>			
		<b>Gost R</b>			
		<b>Electrical insulation:</b> Totally insulated			
		<b>Halogen free (DIN/VDE 0472, Part 815):</b> Yes			
		<b>UV resistance:</b> UL 508			
		<b>Flammability Rating (UL 746 C 5):</b> UL 94 V5			
		<b>Glow Wire Test (IEC 695-2-1) °C:</b> 960			
		<b>NEMA Class:</b> NEMA 1, 3, 3R, 4X, 12, 13			

