

PRODUCT DATA SHEET



PRODUCT CODE: 01480 **DESCRIPTION:** 1/2" DRIVE SOCKET 23MM



INSULATION MATERIAL: NYLON THERMOPLASTIC

LENGTH (MM): 50

METAL MATERIAL: STEEL ALLLOY 31CrV3

WIDTH (MM): 37

SPECIFICATION: IEC60900, CATEGORY 'C', VDE

DEPTH (MM): 37

COUNTRY OF ORIGIN: UNITED KINGDOM

WEIGHT (G): 103

COMMODITY CODE: 8204200000

EAN: 5052269014804



The **ULTIMATE** in electrical and live line protection

ITL has over half a century's worth of experience producing insulated tools to the highest standard possible.

We manufacture unique, injection moulded, insulated tools from Nylon Thermoplastic. All our tools are 100% tested to IEC 60900, Category C and ASTM F1505.

All over the world the professional uses ITL Insulated Tools:

- We are the only company to insulate its tools with a unique injection moulded Nylon Thermoplastic recipe
- Tool and insulation bond as one
- Withstand extreme impact and abrasion
- Flame Retardant
- Stronger and harder than PVC coated tools
- 100% Production Tested –10,000 volts for 3 minutes submerged in water
- Accredited to IEC 60900:2018 – the International Standard for Live Line Working Tools
- Category “C” Impact Tested – for operation within greater temperature range **-40°F to +158°F -40°C to +70°C**
- Lifetime warranty on tool and insulation

