



Click [here](#) for the 3D model.

Dimensions

D	42mm MAX
D2	16.7mm +/-1.0mm
T	17mm MAX

Packaging Specifications

Packaging	Tray, Box
Packaging Quantity	200
Typical Component Weight	57.4 g

General Information

Series	ESD-R-H
Style	Round - Toroidal
Cable Type	Round Cable
Description	EMI Core Solid, For Round Cables, Toroidal Cores
Features	High Heat Resistance, Cable Holding Mechanism
RoHS	Yes
Qualifications	UL94V-0
Case Color	White
Materials	Ni-Zn

Specifications

Temperature Range	-40/+120°C
Effective Frequency	500 MHz (FM Band Range)