



**50%
LESS
EFFORT**

**MORE
POWER**

**CRESCENT
H.K. PORTER®**

Compact Bolt Cutters

Trusted by the Trades.



Compact cutting power with half the effort of standard Lineman's pliers.

Straight Cutter model has center cut blades for longest life. Angle Cutter model has flush cut blades for trimming close. Both have smooth plastic dipped grips for maximum durability and easy clean-up.

For maximum comfort and minimum fatigue, the Spring Return Straight Cutter features co-molded grips and a durable return spring for repetitive-cut production applications. Its straight head and center cut blades make it fast and easy to use.



Induction-hardened cutting edges make quick work of the tough stuff.



WIRE
Copper, vinyl coated,
steel and aluminum



CHAIN
Light duty, hobby,
and craft chain



FASTENERS
Bolts, nails, rivets,
and screws



FENCING
Barbed wire, chicken
wire, hardware cloth



HARD MATERIALS
Spring steel and piano wire

Cutting Applications and Capacities

Material	Maximum Diameter
SOFT (copper, aluminum, plastics, drop ceiling wire)	.24 inches (6.0 mm)
MEDIUM HARD (nails, rivets, wire pins, light chain)	.20 inches (5.2 mm)
HARD (steel wire, wire rope strands, chicken wire)	.16 inches (4.0 mm)
VERY HARD (spring steel, music/piano wire)	.15 inches (3.8 mm)

Item No	Description	Shelf Pack Quantity	UPC	Shelf Pack Code	Product Package Dimensions	Product Weight
0890MC	COMPACT BOLT/WIRE CUTTER, CENTER CUT	6	37103274540	10037103274547	7.3"L x 2.3"W x 1.4"H	0.8 lbs.
0890MA	COMPACT BOLT/WIRE CUTTER, ANGLE HEAD	6	37103274557	10037103274554	7.3"L x 2.3"W x 1.4"H	0.8 lbs.
0890SMC	COMPACT BOLT/WIRE CUTTER, CENTER CUT, CO-MOLD GRP, SPRING LOADED	6	37103274564	10037103274561	7.3"L x 2.3"W x 1.4"H	0.8 lbs.