

Size 15 6-pol st/st m/f PUR 1,5mm² 1,5m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 282 9641 015
Specification	Size 15 6-pol st/st m/f PUR 1,5mm ² 1,5m
HARTING eCatalogue	https://b2b.harting.com/21342829641015

Identification

Category	System cabling
Series	Circular connectors Size 15
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	Size 15 Male Straight
Connector 2	Size 15 Female Straight
Type of cable	Copper cable (round)

Version

Cable length	1.5 m
Number of cores	6
Core structure	6x 1.5 mm ²

Technical characteristics

Rated voltage (signal)	63 V AC/DC
Rated voltage (power)	600 V AC
Rated current (signal)	10 A
Rated current (power)	16 A
Limiting temperature	-25 ... +80 °C
Cable diameter	9 mm



Pushing Performance
Since 1945

Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Black
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

CE	Yes
----	-----

Commercial data

Packaging size	1
Country of origin	Germany
European customs tariff number	85444290
ETIM	EC002599
eCl@ss	27060390 Ready-made data cable (unspecified)