



RD1 Series







ROCKER



Panel Cutout



Terminal Options



FEATURES:

- Compact Size With High Ratings
- Ideal for Applications With Limited Space

SPECIFICATIONS:

RATING: RATING OPTION C:

- 16A 125VAC [UL, cUL]
- 10A 250VAC [UL, cUL]
- 1/3HP 125/250VAC [UL, cUL]
- 10(4)A 250V~ 1E4 T125 [VDE]
- 10(2)A 250V~ 5E4 T85 [VDE]

RATING OPTION 3:

- 10A 125VAC [UL, cUL]
- 6(2)A 250V~ 1E4 T125 [VDE]

TEMPERATURE: -20°C to 105°C [UL, cUL]
-20°C to 125°C [VDE]

ELECTRICAL LIFE: 10,000 Cycles

CONTACT RESISTANCE: 35mΩ Max.

INSULATION RESISTANCE: 100MΩ Min. at 500VDC

DIELECTRIC STRENGTH: 1,500VAC for 1 Minute

MATERIALS:

- Body: Polyamide 6/6, UL94 V-2
- ACTUATOR: Polyamide 6/6, UL94 V-2
- CONTACTS: Silver Alloy
- TERMINALS: Silver Plated Copper



RD11131121



RD11131200



RD111C1900

| Series | Terminal | Function | Rating | Body Color | Actuator Color | Marking Color | Marking Type |
|--------|---------------|----------------------------|----------------------------------|---|--|---|--|
| RD1 | 1 - 4.8mm Tab | 1 - Off-On 4 - Off-(On) | 3 - 10A 125VAC C - 16A 125VAC | 1 - Black 2 - White 3 - Almond 4 - Grey 9 - Red | 1 - Black 2 - White 3 - Almond 4 - Grey 5 - Orange 7 - Blue 8 - Green 9 - Red | 0 - None 1 - Black 2 - White 8 - Red | 0 - None 1 - I/O Vert. 3 - ON/OFF Vert. 4 - ON/OFF Horiz. |

Custom Colors and Markings Available Upon Request

EXAMPLE PART NUMBERS:

- RD11131100 1P Off-On
Black Body/Actuator, No Marking
- RD11131121 1P Off-On
Black Body/Actuator, I/O Vert.
- RD111C1100 1P Off-On
Black Body/Actuator, No Marking
- RD111C1121 1P Off-On
Black Body/Actuator, I/O Vert.

SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE 3/16/2021.



E-SWITCH®

www.e-switch.com

800.867.2717