
KEMET Part Number: KJN102MS35GACZA



KJN SFTY X1-440 Y1-400, Ceramic, Safety, 1000 pF, 20%, 440 VAC (X1), 400 VAC (Y1), Y5U, Lead Spacing = 12.5mm



Dimensions		
D	9mm MAX	
Т	8mm MAX	
S	12.5mm MAX	
F	0.6mm +/-0.1mm	

Packaging Specifications		
Packaging:	T&R, 360mm, H0 = 16mm, Component Pitch = 25.4mm	
Packaging Quantity:	300	

General Information		
Supplier:	KEMET	
Series:	KJN SFTY X1-440 Y1-400	
Style:	Radial Disc	
RoHS:	Yes	
Termination:	Tin	
Failure Rate:	N/A	
Qualifications:	ENEC, cUL, CQC, VDE	

Specifications		
Capacitance:	1000 pF	
Capacitance Tolerance:	20%	
Voltage AC:	440 VAC (X1), 400 VAC (Y1)	
Dielectric Withstanding Voltage:	4,000 V	
Temperature Range:	-25/+85C	
Temperature Coefficient:	Y5U	
Dissipation Factor:	2.5%	
Insulation Resistance:	10 GOhms	
Safety Class:	X1/Y1	

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.

