



Click [here](#) for the 3D model.

### Dimensions

L	170mm NOM
W	95mm NOM
H	80mm NOM
L1	200mm NOM
L2	183mm NOM
W1	60mm NOM
W2	75mm NOM
K	6.5mm NOM
M (Earth)	Threaded Studs M6

### Packaging Specifications

Packaging	Bulk
Packaging Quantity	1
Typical Component Weight	1800 g

### General Information

Series	FLLE2-PV
Style	Chassis Mount
Description	EMI Filter, With Y Capacitor
Features	Single Phase, Photovoltaic Applications
Phase	Single-phase
RoHS	Yes
Qualifications	IEC/EN 60939, UL 1283
Terminal Type	Threaded Studs M6

### Specifications

Voltage DC	1200 VDC
Rated Current	50 A (50°C)
Rated Temperature	55°C
Temperature Range	-40/+100°C
Climate Category	40/100/21
Test Voltage DC (P to P)	1300 VDC
Test Voltage DC (P to E)	1300 VDC
Power Loss	6 W (25°C 50 Hz)