



Click [here](#) for the 3D model.

Dimensions

L	160mm NOM
W	40mm NOM
H	70mm NOM
L1	180mm NOM
L2	190mm NOM
W1	20mm NOM
J	22mm NOM
K	4.5mm NOM
M (Earth)	Threaded Studs M5

Packaging Specifications

Packaging	Bulk
Packaging Quantity	1
Typical Component Weight	500 g

General Information

Series	FLLD3-MH
Style	Chassis Mount
Description	EMI Filter, Chassis Mount, Motor Drives
Features	Three Phase, High Performance, High Voltage
Phase	Three-phase
RoHS	Yes
Qualifications	IEC/EN 60939, UL 1283
Terminal Type	Threaded Studs M5

Specifications

Voltage AC	530 VAC, 305 VAC
Rated Frequency	50-60 Hz
Rated Current	7 A (50°C)
Rated Temperature	50°C
Temperature Range	-25/+100°C
Climate Category	25/100/21
Test Voltage DC (P to P)	2250 VDC
Test Voltage DC (P to E)	3000 VDC
Power Loss	4 W (25°C 50 Hz)
Leakage Current	3.1 mA